

Datasheet

SIVA purified MaxPab mouse polyclonal antibody (B02P)

[provided by RefSeq]

Catalog Number: H00010572-B02P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human SIVA protein.

Immunogen: SIVA (NP_006418, 1 a.a. ~ 175 a.a) full-length human protein.

Sequence:

MPKRSCPFADVAPLQLKVRVSQRELSRGVCAERYSQ
EVFEKTKRLLFLGAQAYLDHVWDEGCAVVHLPESPKP
GPTGAPRAARGQMLIGPDGRLIRSLGQASEADPSGVA
SIACSSCVRAVDGKAVCGQCERALCGQCVRTCWGCG
SVACTLCGLVDCSDMYEKLCTSCAMFET

Host: Mouse

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10572

Gene Symbol: SIVA1

Gene Alias: CD27BP, SIVA, Siva-1, Siva-2

Gene Summary: This gene encodes a protein with an important role in the apoptotic (programmed cell death) pathway induced by the CD27 antigen, a member of the tumor necrosis factor receptor (TNFR) superfamily. The CD27 antigen cytoplasmic tail binds to the N-terminus of this protein. Two alternatively spliced transcript variants encoding distinct proteins have been described.